

**Features:**

- Three wide range high-power categories
- Flat spectrum with negligible residual Fabry-Perot modulation depth

**Packages:**

- **Fiber coupled** – Butterfly, DIL
- **Free space** – TOW 1, 2

**Additional & customized:**

- PD monitors
- FC/APC terminated pigtailed
- PM pigtailed (polarized or pseudo-depolarized output emission ex PM fiber)

**Applications:**

- fiberoptic gyros
- fiberoptic sensors
- optical coherence tomography
- optical measurements

**PERFORMANCE EXAMPLES**

**Specifications (Nominal Emitter Stabilization Temperature +25 °C)**

Parameter	Category	Min	Typ.	Max
Output power ex SM fiber, emitter @ +25 °C, mW	HP1	-	-	10.0
	HP2	-	-	20.0
	HP3	-	-	30.0
Output power, Glass Window, emitter @ +25 °C, SLD-38-HP*, mW	HP1	-	-	25.0
	HP2	-	-	40.0
	HP3	-	-	50.0
Forward current, mA	HP1	-	150	250
	HP2	-	220	300
	HP3	-	300	350
Forward voltage, V	All	-	-	2.8
Peak wavelength, nm	All	790	830	860
Spectrum width, nm	HP1,HP2**	13	18	-
	HP3**	10	14	-
Slow / fast polarization ratio (PM-polarized modules)***, dB	All	6	7	15
Residual spectral modulation depth, %	All	-	2.0	5.0
Secondary coherence subpeaks, dB (10 log)	All	-	-20	-
Operating temperature (case), °C	All****	-55	-	+60
Cooler current, A	All	-	-	1.2
Cooler voltage, V	All	-	-	3.5

- \* TOW2 packaged SLDs
- \*\* Depends on center wavelength selected, call for more details
- \*\*\* Pseudo-depolarized versions (light is launched into the fiber with its polarization oriented at 45° to the birefringent axes) are available upon request
- \*\*\*\* I) here rated for butterfly packaged modules  
II) may be extended for HP1 and HP2 rated modules

The following part numbers should be used when **ordering**:

SLD-38(a)-(b)-(c)-(d)-(e),  
 where: (a) – 0 (free space) or 1 (fiber pigtailed),  
 (b) – power category (HP1, HP2, HP3), (c) – package type,  
 (d) – SM (isotropic) or PM (polarization maintain) fiber (pigtailed versions only), (e) – PD (if PD monitor is required).




Example: SLD-381-HP2-DIL-SM-PD.

Attention: SLD center wavelength is not guaranteed unless not specified in PO body.

**A maximum feedback of 10<sup>-3</sup> is allowed to run HP series SLDs safely at full power.**

All specifications are subject to change without notice.

**A lot of customized solutions are available — contact us with your detailed requirements!**



Mirror displacement = Optical path difference / 2