

## Features

- ▶ Typical wavelength, 637nm
  - ▶ Stabilized optical power 6mW
  - ▶ Single supply voltage, 5V DC
  - ▶ **Line generator : Cylindrical glass lens**
  - ▶ **Precisely adjustable line thickness**
  - ▶ **3 elements optic structure**  
(2 lens fixed, 1 lens mobile)
  - ▶ **Modulation : digital, analog ~300KHz**
  - ▶ **Wire length : 30cm(standard) or custom**
  - ▶ **Laser class : 1M,2M,3R (IEC 60825-1)**
- ◆ **Option : Bracket & Power supply.**

## Specification

### ● Optical

Optical power(mW)	6 (Tc=25°C)
LD power(mW)	10 (Max)
Wavelength(nm)	637 ±8
Focus Beam Wid(mm)	< 0.1 (at 300mm)
Collimated Beam Wid(mm)	<3 (at 10m)
Fan Angle ( ° )	15,30,45,60,90, 120
Line Pattern	Accurate Straight
Beam Quality	TEM00
Beam intensity Pattern	Gaussian
LD Pin Connection	Case Ground

### Electrical

Operating voltage(DC V)	5 ± 5%
Operating current(mA)	70 (Typ.)
Drive circuit	APC
Operating Temp.(°C)	-10 ~ +60
Storage Temp.(°C)	-40 ~ +85

### Mechanical


Weight(g)	26 ± 0.5
Dimensions(mm)	14Φ X 80
Operating lifetime(h)	30,000~50,000 (@RT)
Housing material	Aluminum

## Description

The MS series laser diode module combines laser diode technology, 3 elements lens optics, and sophisticated electronics within a slim and light aluminum anodized housing. Specially, 3 lens structure compensates line beam's curve & unbalance and dot beam's accurate focused point.

This series of modules provides a high-brightness elliptical laser line, and have various wavelengths and optical output power. Applications include a measurement, positioning, lighting, alignment, guidelines, pointing, switching, leveling, and machine vision etc. Useful in a variety of medical, industrial, and scientific instrumentation, as well as general R&D work.

## Drawings



### \* Range of fan angle

Symbol	Angle	Line length [ mm ] (distance 1m)	
		Perpendicular	Inclined at45°
1D	15°	250	500
3D	30°	500	1200
4D	45°	830	2000
6D	60°	1160	3500
9D	90°	2000	About 5000
12D	120°	3400	About 8000

### Lanics Co., Ltd.

Room #703, 7F Woolim e-Biz Center  
170-5, Guro-dong, Guro-gu, Seoul, 152-050, Korea  
TEL : +82-2-2108-2255 FAX : +82-2-2108-2260

E-mail : [support@lanics.com](mailto:support@lanics.com)

[http:// www.lanics.com](http://www.lanics.com)